



AC 800PEC, SV 5.1 components price list valid from 1.01.07 until 31.12.07

ABB Number	Type	List price
PP D113 B, Controller Box		
3BHE020457R0001	PP D113 B01: AC 800PEC Basic Module, FPGA Size 10K	SFr. 23'108.00
3BHE020457R0101	PP D113 B101: AC 800PEC Basic Module, FPGA Size 10K, varnished	SFr. 24'788.00
3BHE020457R0011	PP D113 B11: AC 800PEC Basic Module, FPGA Size 20K	SFr. 27'090.00
3BHE020457R0111	PP D113 B111: AC 800PEC Basic Module, FPGA Size 20K, varnished	SFr. 28'575.00
3BHE020457R0021	PP D113 B21: AC 800PEC Basic Module, FPGA Size 30K	SFr. 28'608.00
3BHE020457R0121	PP D113 B121: AC 800PEC Basic Module, FPGA Size 30K, varnished	SFr. 30'723.00
AnyIO Communication Modules		
3BHE017012R0001	XU D150 B01: PEC800-CEX1 RS232	SFr. 1'970.00
3BHE017012R0101	XU D150 B101: PEC800-CEX1 RS232 varnished	SFr. 2'122.00
3BHE017012R0002	XU D150 B02: PEC800-CEX2 RS422	SFr. 1'970.00
3BHE017012R0102	XU D150 B102: PEC800-CEX2 RS422, varnished	SFr. 2'126.00
3BHB010695R0002	AnyBus-S Profibus-DP Slave Pin 8,1(AB4177)	SFr. 1'565.00
3BHB010695R0102	AnyBus-S Profibus-DP Slave Pin 8,1 varnished	SFr. 1'668.00
3BHE010984R0002	AnyBus-S CAN open, Pin 8,1 (AB4313)	SFr. 1'773.00
3BHE010984R0102	AnyBus-S CAN open, Pin 8,1, varnished	SFr. 1'876.00
3BHB010693R0002	AnyBus-S Ethernet Modbus/TCP Pin 8,1 (AB4314)	SFr. 1'732.00
3BHB010693R0102	AnyBus-S Ethernet Modbus/TCP Pin 8,1 varnished	SFr. 1'835.00
3BHE011104R0002	AnyBus-S Modbus RTU Slave Pin 8,1 (AB4343)	SFr. 1'589.00
3BHE011104R0102	AnyBus-S Modbus RTU Slave Pin 8,1 varnished	SFr. 1'692.00
3BHE018697R0002	AnyBus-S Device Net Pin 8,1 (AB4035)	SFr. 1'338.00
3BHE018697R0102	AnyBus-S Device Net Pin 8,1 varnished	SFr. 1'440.00
EHBC690033R0001	AnyBus-S Control Net Slave Pin 8,1 (AB4496)	SFr. 2'135.00
EHBC690033R0101	AnyBus-S Control Net Slave Pin 8,1 varnished	SFr. 2'238.00
UF D128/130/131/132 Optical Modules		
3BHE012049R0001	UF D128 A01: OM -I-6-V10	SFr. 428.00
3BHE012049R0101	UF D128 A101: OM -I-6-V10, varnished	SFr. 528.00
3BHS018799R0001	UF D127A01 OM-I-6-S5 5MB GOF	SFr. 771.00
3BHS018799R0101	UF D127A01 OM-I-6-S5 5MB GOF, varnished	SFr. 802.00
3BHE013570R0001	UF D130 A01 OM-I-6-S32	SFr. 1'489.00
3BHE013570R0101	UF D130 A101 OM-I-6-S32, varnished	SFr. 1'547.00
3BHE014377R0001	UF D131 A01 Opt. Module O-x-x-xxx, TX	SFr. 556.00
3BHE014377R0101	UF D131 A101 Opt. Module O-x-x-xxx, TX, varnished	SFr. 685.00
3BHE014551R0001	UF D132 A01 Opt. Module I-x-x-xxx, RX	SFr. 685.00
3BHE014551R0101	UF D132 A101 Opt. Module I-x-x-xxx, RX, varnished	SFr. 685.00
UA D149 A, Combi I/O		
3BHE014135R0000	UA D149 A01:Combi I/O Box (basic kit/rack, and one opt. Module)	SFr. 3'671.00
3BHE014136R0000	UA D149 A01: Combi I/O Box (as per above), varnished	SFr. 4'134.00
3BHE014135R0001	UA D149 A01: Combi I/O (box with optical module and mixed module)	SFr. 6'300.00
3BHE014135R0011	UA D149 A01: Combi I/O (box w. optical mod. and with 2 mixed mod.)	SFr. 8'928.00
3BHE014136R0011	UA D149 A01: Combi I/O (box w. opt.mod. & with 2 mixed mod.) varnished	SFr. 10'213.00
3BHE012095R0001	UA D141 A01: Combi I/O Basic board	SFr. 2'292.00
3BHE012095R0101	UA D141 A101: Combi I/O Basic board varnished	SFr. 2'559.00
3BHE012095R0002	UA D141 A02: Combi I/O Basic board flash	SFr. 2'659.00
3BHE012095R0102	UA D141 A102: Combi I/O Basic board flash varnished	SFr. 2'926.00
3BHE012551R0001	UA D142 A01: Combi I/O Mixed Module	SFr. 2'628.00
3BHE012551R0101	UA D142 A101: Combi I/O Mixed Module varnished	SFr. 2'844.00
3BHE012276R0001	UA D143 A01: Combi I/O Traction	SFr. 1'849.00
3BHE012276R0101	UA D143 A101: Combi I/O Traction varnished	SFr. 1'959.00
Equipped with Optical Modules type UF D128 or UF D130, as per above		
PV D164 A, PEC INT		
3BHE014340R0000	PV D164 A01: Basic kit/rack (without Optical Modules)	SFr. 4'254.00
	PV D164 A101: Basic kit/rack (as per above) varnished	SFr. 4'357.00
3BHE013854R0001	PD D163 A01: PEC Interface Board 15-80-R-C-4	SFr. 2'515.00
3BHE013854R0101	PD D163 A101: PEC Interface Board 15-80-R-C-4 varnished	SFr. 2'720.00
3BHE013854R0002	PD D163 A02: PEC Interface Board 30-1000-R-I-6	SFr. 2'666.00
3BHE013854R0102	PD D163 A102: PEC Interface Board 30-1000-R-I-6 varnished	SFr. 2'871.00
3BHE013854R0003	PD D163 A03: PEC Interface Board 15-500-FP-C-4	SFr. 2'913.00
3BHE013854R0103	PD D163 A103: PEC Interface Board 15-500-FP-C-4 varnished	SFr. 3'118.00
Equipped with upto 6 Optical Modules, as per above		

GD D160 A & GD D165 A, PEBB Interface		
3BHE012548R0101	GD D160 B101: PEBB Interface Board varnished	SFr. 4'357.00
3BHE014311R0001	GD D165 A01: PEBB Interface Quad	SFr. 3'386.00
3BHE014311R0101	GD D165 A101: PEBB Interface Quad varnished	SFr. 3'671.00
UA D144 A, PECMI		
3BHE016842R0001	UA D144 A01: PECMI-Board	SFr. 2'249.00
3BHE016842R0101	UA D144 A101: PECMI-Board varnished	SFr. 2'365.00
UU D148 A, CT/VT Module		
3BHE014185R0001	UU D148A01: VT Board	SFr. 1'695.00
3BHE014185R0101	UU D148A101: VT Board varnished	SFr. 1'839.00
3BHE014185R0002	UU D148A02: 1A-CT Board	SFr. 1'719.00
3BHE014185R0102	UU D148A102: 1A-CT Board varnished	SFr. 1'863.00
3BHE014185R0003	UU D148A03: 5A-CT Board	SFr. 1'667.00
3BHE014185R0103	UU D148A103: 5A-CT Board varnished	SFr. 1'812.00
3BHE014658R0101	XF D151 A101 CAN converter board varnished	SFr. 594.00
Cables, Accessoires, Tools		
3BHE014317R0001	CEX Cable, RS232, 0,3 meters	SFr. 282.00
3BHE014317R0002	CEX Cable, RS232, 0,5 meters	SFr. 285.00
3BHE014317R0003	CEX Cable, RS232, 0,7 meters	SFr. 289.00
3BHE014142R0100	XU D150, RS422 Cable, 1 meter	SFr. 247.00
3BHE012361R0200	Patchcable Ethernet RJ45, 2 meters	SFr. 145.00
3BHE004263P0171	Patchcable Kat. 5 STP crossed, 3 meters	SFr. 83.00
3BHE015519R0001	AC 800PEC Servicecable Com4 - SubD, 5 meters	SFr. 157.00
3BHL000986P7002	AC/DC converter dual 250W, Power One type LWN 2660-6	SFr. 848.00
3BSC950193R0001	TB850 CEX Bus Terminator (25-pin DB25P male connect. screw fix.)	SFr. 52.00
3BHE018137R0001	XU D194 A Commissioning Interface Box	SFr. 6'600.00

Control IT software licences:

Control IT software licence fees are included in the hardware prices of the PP D113B (Power Electronics Controller).

Small order surcharge:

Orders with a value less than CHF 1000.00 are subject to a small order surcharge of CHF 250.00.

Terms of delivery:

Ex Works Turgi, standard packing included.

Guarantee:

12 months from date of dispatch.

Varnished versions:

Price and delivery time for the varnished versions should to be confirmed by us, prior placing the order.

Discount:

For aggregated AC 800PEC orders of the same type, we will grant the following discounts:

- 5 to 9 pcs.: 6%
- 10 to 14 pcs.: 9%
- 15 to 24 pcs.: 12%
- 25 to 34 pcs.: 15%
- from 35 pcs.: 18%