



“VAR-TALK”:SPECIALTY CAPACITORS–SURGE PROTECTION

Capacitor Division 500 Rue du Binome Quebec, QC, Canada G1P 4P1 Tele. #418-650-9224 FAX #418-650-1883

Unit Voltage	# of Poles	UF / Pole	ABB Quebec 2GUS03180	ABB U. K. ESG3180	ABB Bloomington 2SG3180A	Westinghouse Bloomington WEMCOL - 2	Westinghouse Bloomington WEMCOL - 1	Westinghouse Bloomington PCB – F/P	Westinghouse Bloomington PCB – 2	Westinghouse Bloomington PCB - 1	General Electric
0 – 650	3	1.0				1NO2180A05	1NO2180A05	366C970G03	366C970G03		
2400	3	0.5						278C180A02	4A3399G02	1114725	
4160	3	0.5	3A7	A07	A07	1NO3180A07	1NO2180A07	278C180A04	4A3399G03	1114727	
6900	3	0.5						278C180A07	259B995A01		
7200	3	0.5	3A1	A01	A01	1NO3180A01	1NO2180A01	278C180A14			18L0065WH
13800	3	0.25	3A9	A09	A09	1NO3180A09	1NO2180A09				18L0012WH
2400	2	0.5							4A3399G01	1114724	
14400	2	0.5	2A6	A06	A06	1NO3180A06	1NO2180A06				
2400	1	0.5						278C180A01	4A1948G01	1113723	18L0015WH
4160	1	0.5						278C180A03	4A1948G02	1114726	18L0015WH
4800	1	0.5						278C180A05	4A1949G04	1151989	
6900	1	0.5						278C180A06	4A1949G01	1114728	18L0019WH
7200	1	0.5	1A2	A02	A02	1NO3180A02	1NO2180A02				
10500	1	0.25							4A1949G06		
11500	1	0.25						278C180A08	4A1949G02	1114729	
13800	1	0.25	1A3	A03	A03	1NO3180A03	1NO2180A03	278C180A09	4A1949G03	1114730	18L0009WH
13800	1	0.75	1A15	A15	A15	1NO3180A15					
18000	1	0.13						278C180A10	4A1949G08	1733250	
24000	1	0.83	1A5	A05							
24000	1	0.13	1A4	A04		1NO3180A04	1NO2180A04	278C180A11		505D340G01	18L0010WH
24000	1	0.15	1A40	ESG24015							
6600*	1	0.10				634A269A01	634A169A01	633A918A01			
13800*	1	0.15				634A269A02	634A169A02	633A918A02			
50/100DC		1/0.25					1NO2700A01	6A1377G01	6A1377G01	1166999	
750 DC		0.5					1NO2853A18				

* - Radiation Resistant/No Fluid/Ceramic Envelop

WARNING : Vintages and style numbers are NOT physically interchangeable; check unit outline before purchasing and applying !!!