




We reserve all rights in this document and in the information contained therein. Reproductions, use for other than intended purposes, or distribution without the written consent of ABB Network Partner AB is strictly forbidden.



3-PH VOLTAGE RESTRAINT  
OVERCURRENT PROTECTION  
3-FAS SPÄNNINGSSTABILISERAT  
ÖVERSTRÖMSSKYDD  
24C



101 RXTUG 22H  
107,113, 119 RXISK 2H

- 1) BLOCKING OF I/U> FUNCTIONS  
BLOCKERING AV I/U> FUNKTIONERNA
- 2) RESETTING OF INDICATION  
ÅTERSTÄLLNING AV INDIKERING
- 3) VOLTAGE RESTRAINT OVERCURRENT,  
START  
SPÄNNINGSSTABILISERAD ÖVERSTRÖM,  
START
- 4) VOLTAGE RESTRAINT OVERCURRENT,  
TRIPPING  
SPÄNNINGSSTABILISERAD ÖVERSTRÖM,  
UTLÖSNING
- 5) OVERCURRENT, TRIPPING  
ÖVERSTRÖM, UTLÖSNING
- 6) LOSS OF AUXILIARY VOLTAGE  
BORTFALL AV HJÄLPSPÄNNING
- 7) CONNECTED FOR RL=110-220V DC  
CHANGE FFROM 111 TO 112 AND  
121 TO 122 AT RL=48-60V DC  
KOPPLAD FÖR RL=110-220V DC  
ÄNDRA FRÅN 111 TILL 112 OCH  
121 TILL 122 VID RL=48-60V DC

ELCAD ID PS/render      DATE 2004-06-2122:35      IMRK 000 076-YA      Issued in ARCADE

|                             |  |   |  |                 |  |
|-----------------------------|--|---|--|-----------------|--|
| Prepared 97-05-28 H RAZA/LB |  | CIRCUIT DIAGRAM/KRETSSHEMA              |  | + .             |  |
| Approved 97-08-01 P JENÄKER |  | RAISK 3 3-PH. VOLT. RESTRAINT O/C PROT. |  | Lang 82         |  |
| Rev Ind Revision            |  | RAISK 3 3-FAS SP.STAB. ÖVERSTRÖMSSKYDD  |  | Rev Ind -       |  |
| Reg No 7411                 |  | Resp dep PS                             |  | Lang 82         |  |
| Based on Pcl 890.562        |  | ABB ABB Network Partner AB              |  | IMRK 001 077-YA |  |
|                             |  |   |  | Sheet 1         |  |
|                             |  |   |  | Cont            |  |