

Product note

New Tmax adapters for the Fastline system



T5, T4 and T2 Adapters with Tmax circuit breakers installed



T6 and T7 Adapters with Tmax circuit breakers installed

Tmax Adapter

The Tmax Adapters are designed for mounting the Tmax circuit breakers into the FastLine distribution system. We can now offer the following range of FastLine Tmax adapters :

- 3-pole for T2, T4, T5, T6 and T7
- 4-pole for T2, T4, T5 and T6

The T2-T6 Adapters can also be delivered with a cut-out in the front panel for monitoring instruments.

The FastLine System

- This is a modular system consisting of :
 - Busbar plates type FS or FST, 400 - 2500 A widths 150 - 1600 mm.
- Incoming feeding modules
- Fuse switch modules, 160 - 630 A
- Tmax Adapters for Tmax circuit breakers T2 - T7

All the modules and adapters have integrated plug contacts at the rear side for easy plug in at the FS or FST busbar plates.

Advantages of the FastLine System

- Complete distribution system up to 2500 A
- Very fast and easy assembly
- Modular design and system
- Safe flexibility to plug the modules on and off live busbars
- Can be installed vertical or horizontal

By using the FastLine system and the Tmax Adapters, you will have a complete distribution board with high flexibility by pluggable modules on a live system.

Areas of application :

- Cable Distribution Cabinets (CDC)
- Transformer substations
- Switchboards for industry
- Car industry (high flexibility)
- Railway installations

FastLine is the best “plug and play” system for an engineer.

Standard adapters

1SEP304557R0001	T2 3p	160A	100mm
1SEP304604R0001	T4 3p	320A	150mm
1SEP304605R0001	T5 3p	440A	200mm
1SEP102236R0003	T6 3p	850A	250mm
1SEP102237R0003	T7 3p	1100A	250mm

1SEP304653R0001	T2 4p	160A	150mm
1SEP304654R0001	T4 4p	320A	200mm
1SEP304655R0001	T5 4p	440A	250mm
1SEP102236R0004	T6 4p	850A	300mm

Adapters with measuring possibilities (Multimeter)

1SEP304557R0003	T2 3p	160A	100mm
1SEP304604R0001	T4 3p	320A	150mm
1SEP304605R0001	T5 3p	440A	200mm
1SEP102236R0013	T6 3p	850A	250mm

1SEP304653R0003	T2 4p	160A	150mm
1SEP304654R0003	T4 4p	320A	200mm
1SEP304655R0003	T5 4p	440A	250mm
1SEP102236R0014	T6 4p	850A	300mm

All adapters are delivered as empty units for mounting the Tmax circuit breaker locally by the end user.

Please note the following:

ISOMAX S6 and S7 adapters are now taken out of our product range and are no longer available. By this the whole ISOMAX adapter range is now completely replaced by the new Tmax adapter range.

For more information please contact:

ABB AS

Automation Products Division

P.O. Box 100 Sentrum

3701 Skien, Norway

Phone: +47 35 58 25 00

www.abb.com/fusegear



T6 adapter 3-pole