

Dissolved Oxygen Cartridge Flow System

With Water-wash Option
9408 Series

- **Bayonet-fit flow system**
 - easy, no-fuss sensor removal for calibration
- **Choice of process connections**
 - BSP and NPT
- **Replaceable oxygen sensor**
 - simplifies maintenance and eliminates the need to replace the membrane
- **Choice of cable lengths**
 - to suit a wide range of installation demands
- **Water-wash option**
 - minimizes maintenance and optimizes performance




**A robust, compact, dissolved
oxygen system for continuous
on-line monitoring**

Introduction

These compact and robust flow systems complement the highly successful 9408 floating ball, dip and submersible systems and employ the well-proven 8012 oxygen sensor.

A key feature is the bayonet snap-fit connection which makes removal for calibration extremely easy and convenient. The typical life of the 8012 oxygen sensor is 12 months, although many users benefit from a much longer operational period. The sensor is extremely rugged and can be used in the most demanding environments.



Bayonet Snap-fit Connection

Specification

Materials of construction

Glass-coupled polypropylene

Operating temperature range

-5 to 40°C (23 to 104°F)

Operating pressure

Atmospheric

Temperature compensation

Automatic correction by means of an integral Pt100 resistance sensor

Accuracy

±0.2mg/l or ±2% saturation within ±10°C (50°F) of the calibration temperature within the range 0 to 35°C (32 to 95°F)

Response

Typically 20s for 90% step change of oxygen concentration at 20°C (68°F)

Pressure rating

2 Bar

Flow rate

2 l/minute minimum

Process connections


1/2 in. & 1 in. BSP and 1/2 in. & 1 in. NPT

Cable lengths*

1, 3, 5, 10 and 20m (3, 9, 15, 30 and 60 ft approx.) standard options

*Note. With a suitable junction box a maximum of 100m (300 ft.) extension cable can be used (part no. 0233/828).

Overall Dimensions



Ordering Information

9408 Series Dissolved Oxygen Cartridge Flow System	9408/8	X	X	X
Process Connections				
1 in. BSP		0		
1/2 in. BSP		1		
1 in. NPT		2		
1/2 in. NPT		3		
Cable Length				
1m (3 ft)			0	
3m (9 ft)			1	
5m (15 ft)			2	
10m (30 ft)			3	
20m (60 ft)			4	
Cleaning				
Without cleaning				0
With cleaning				2

ABB has Sales & Customer Support
expertise in over 100 countries worldwide

www.abb.com

The Company's policy is one of continuous product
improvement and the right is reserved to modify the
information contained herein without notice.

Printed in UK (11.06)

© ABB 2006



ABB Limited

Oldends Lane, Stonehouse
Gloucestershire
GL10 3TA
UK
Tel: +44 (0)1453 826661
Fax: +44 (0)1453 829671

ABB Inc.

Analytical Instruments
9716 S. Virginia St. Ste., E
Reno, Nevada 89521
USA
Tel: +1 775 850 4800
Fax: +1 775 850 4808