



Refurbishing the Sensor

- 1) Close the valve upstream of the monitor and allow the constant head unit to empty or pinch off the line from it to the sensor.
- 2) Pull the hydrazine sensor out of its mounting clips on the sub-panel. Disconnect the electrical leads at the plug and socket.
- 3) Holding the sensor over the drain tundish, pull off the sample inlet tube and let the tube and sensor cell drain. Leave the end of the inlet tube dipping into the tundish.

- 4) Carefully pull the sensor apart and wash the components thoroughly to remove all traces of gel.
- 5) Withdraw the platinum electrode, taking care not to damage the electrode or the electrical connection. Insert the brush supplied in the sensor kit down the bore of the ceramic tube; rotate gently and withdraw. Clean the platinum anode by immersing it in a test tube containing 50% nitric acid for a few minutes.

Caution. Do not to let the acid touch the rubber bung.

- 6) If the silver cathode is tarnished or blackened, dip a cotton wool bud in 50% nitric acid and run this over the wire to restore it to a matt silver finish. Rinse thoroughly with high purity water.
- 7) Assemble the sensor and fill with GEL as follows:
- 8) Holding the white closure cap tightly in place on the filling syringe, snap the syringe plunger into position and then remove the white closure cap.
- 9) Place the blue Luer fitting on the syringe nozzle.
- 10) Slowly inject the filling gel through the bottom hole in the outer jacket of the sensor until it reaches the top hole.
- 11) Remove the syringe and replace its closure cap.
- 12) Push the sensor into the clips of the sub-panel – the clips incorporate small protrusions which cover the filling and exit holes in the outer jacket.
- 13) Connect the tube from the mixing coil to the bottom of the sensor.

Note. Hold the sensor firmly at the top so that the centre portion is not pushed out when the tube is connected.

- 14) Plug the electrical connection into the socket at the top of the liquid handling panel.

Continued...

- 15) Fill the reagent and calibration solution containers with their respective solutions and open the valve on each reservoir by unscrewing two turns.

Warning. The sample will be dosed with sodium hydroxide and the concentration, although small at first, will increase if any spillage is left to evaporate. Dispose of the outflow safely.

- 16) Open the shutoff valve upstream of the sensor unit and adjust until sample is overflowing from the constant head unit but not fast enough to reach the emergency overflow.
- 17) Ensure that the flow through the sensor is at the correct rate (see 7835 manual).
- 18) Close and lock the sensor unit door.
- 19) Carry out a calibration sequence as described in the 7835 manual.

ABB has Sales & Customer Support expertise in over 100 countries worldwide

www.abb.com

The Company's policy is one of continuous product improvement and the right is reserved to modify the information contained herein without notice.

Printed in UK (06.06)

© ABB 2006



ABB Limited
Oldends Lane, Stonehouse
Gloucestershire
GL10 3TA
UK
Tel: +44 (0)1453 826661
Fax: +44 (0)1453 829671

ABB Inc.
125 E. County Line Road
Warminster
PA 18974
USA
Tel: +1 215 674 6000
Fax: +1 215 674 7183