



FM Approvals
1151 Boston Providence Turnpike
P.O. Box 9102 Norwood, MA 02062 USA
T: 781 762 4300 F: 781-762-9375 www.fmapprovals.com

Member of the FM Global Group

CERTIFICATE OF COMPLIANCE

HAZARDOUS LOCATION ELECTRICAL EQUIPMENT PER CANADIAN REQUIREMENTS

This certificate is issued for the following equipment:

FEP315abcdefghijklmnop1opqr ProcessMaster Electromagnetic Flowmeter – Integral version

NI / I, II / 2 / ABCDFG / T* Ta = -40°C to +60°C; Type 4X: IP65

S / III / T* Ta = -40°C to +60°C; Type 4X: IP65

DIP / II, III / 1 / EFG / T* Ta = -40°C to +60°C; Type 4X: IP65

a = 3 digit number representing the bore diameter; 003, 004, 006, 008, 010, 015, 020, 025, 032, 040, 050, 065, 080, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700, 760, 800, 900, 001, 201, 401, 601, 801, or 002.

b = liner material; A, E, F, H, P, S, or U.

c = Electrode design; 1, 2, 5, or 6.

d = Measuring electrode material; A, D, E, F, G, H, J, K, N, S, or W.

e = Grounding accessories; 1, 2, 3, or 4.

f = Process connection type; D0, D1, D2, D3, D4, D5, D6, A1, A3, A6, A7, A8, A9, J1, J2, J3, E1 or E2.

g = Process connection material; B, C, or D.

h = Usage certifications; 0, 1, 2, 3, 4, 5, 6, or 7.

i = Calibration type; A, B, K, L, M, or T

j = Temperature range of sensor/Ambient temperature range; 1, 2, 3, or 4.

k = Name plate language and type; A, B, or C

o = Cable Conduits; A, B, or C.

p = Power supply; 1, 2, 3, or 4.

q = Input and output signal type; A, B, C, or D.

r = Configuration type/Diagnostics; 1, 2, 3 or 4.

FEP325abcdefghijklmnop1o0Yrs - ProcessMaster Electromagnetic Flowmeter – Remote version

NI / I, II / 2 / ABCDFG / T* Ta = -40°C to +60°C; Type 4X: IP65

S / III / T* Ta = -40°C to +60°C; Type 4X: IP65

DIP / II, III / 1 / EFG / T* Ta = -40°C to +60°C; Type 4X: IP65

a = 3 digit number representing the bore diameter; 003, 004, 006, 008, 010, 015, 020, 025, 032, 040, 050, 065, 080, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700, 760, 800,



Member of the FM Global Group

- 900, 001, 201, 401, 601, 801, or 002.
- b = liner material; A, E, F, H, P, S, or U.
- c = Electrode design; 1, 2, 5, or 6.
- d = Measuring electrode material; A, D, E, F, G, H, J, K, N, S, or W.
- e = Grounding accessories; 1, 2, 3, or 4.
- f = Process connection type; D0, D1, D2, D3, D4, D5, D6, A1, A3, A6, A7, A8, A9, J1, J2, J3, E1 or E2.
- g = Process connection material; B, C, or D.
- h = Usage certifications; 0, 1, 2, 3, 4, 5, 6, or 7.
- i = Calibration type; A, B, K, L, M, or T
- j = Temperature range of sensor/Ambient temperature range; 1, 2, 3, or 4.
- k = Name plate language and type; A, B, or C
- l = Signal Cable length and type 0, 1, 2, 3, 4, 5, 6, 7, or 8.
- o = Cable Conduits; A, B, or C.
- p = Power supply; 1, 2, 3, or 4.
- q = Input and output signal type; A, B, C, or D.
- r = Configuration type/Diagnostics; 1, 2, 3 or 4.
- s = Accessories; AP or blank

FEH315abcdefghijk0P1opqrs HygienicMaster Electromagnetic Flowmeter – Integral version

NI / I, II / 2 / ABCDFG / T* Ta = -40°C to +60°C; Type 4X: IP65

S / III / T* Ta = -40°C to +60°C; Type 4X: IP65

DIP / II, III / 1 / EFG / T* Ta = -40°C to +60°C; Type 4X: IP65

- a = 3 digit number representing the bore diameter; 003, 004, 006, 008, 010, 015, 020, 025, 032, 040, 050, 065, 080, or 100.
- b = liner material; A, or P.
- c = Electrode design; 1, 2, 5, or 6.
- d = Measuring electrode material; A, D, E, F, G, H, J, K, N, S, or W.
- e = Grounding accessories; 1, or 2.
- f = Process connection type; D2, D4, D5, D6, A1, A3, J1, J2, J3, M1, F1, R1, R2, R3, R4, R5, R6, T1, T2, T3, W1, or Y0.
- g = Process connection material; C, D, E, F, G, H, W, or Y.
- h = Usage certifications; 0, 1, 2, 3, 4, 5, 6, or 7.
- i = Calibration type; A, B, K, L, M, or T
- j = Temperature range of sensor/Ambient temperature range; 1, 2, 3, or 4.
- k = Name plate language and type; A, B, or C.
- o = Cable Conduits; A, B, or C.
- p = Power supply; 1, 2, 3, or 4.
- q = Input and output signal type; A, B, C, or D.
- r = Configuration type/Diagnostics; 1, 2, 3 or 4.

FEH325abcdefghijkIP1o0Yrs HygienicMaster Electromagnetic Flowmeter – Remote version

NI / I, II / 2 / ABCDFG / T* Ta = -40°C to +60°C; Type 4X: IP65

S / III / T* Ta = -40°C to +60°C; Type 4X: IP65

DIP / II, III / 1 / EFG / T* Ta = -40°C to +60°C; Type 4X: IP65

- a = 3 digit number representing the bore diameter; 003, 004, 006, 008, 010, 015, 020, 025, 032, 040, 050, 065, 080, or 100.
- b = liner material; A, or P.
- c = Electrode design; 1, 2, 5, or 6.
- d = Measuring electrode material; A, D, E, F, G, H, J, K, N, S, or W.
- e = Grounding accessories; 1, or 2.
- f = Process connection type; D2, D4, D5, D6, A1, A3, J1, J2, J3, M1, F1, R1, R2, R3, R4, R5, R6, T1, T2, T3, W1, or Y0.
- g = Process connection material; C, D, E, F, G, H, W, or Y.



Member of the FM Global Group

h = Usage certifications; 0, 1, 2, 3, 4, 5, 6, or 7.
i = Calibration type; A, B, K, L, M, or T
j = Temperature range of sensor/Ambient temperature range; 1, 2, 3, or 4.
k = Name plate language and type; A, B, or C
l = Signal Cable length and type; 0, 1, 2, 3, 4, 5, 6, 7, or 8
o = Cable Conduits; A, B, or C.
r = Configuration type/Diagnostics; 1, 2, 3 or 4.
s = Accessories; AP or blank

FET325jk0P1opqr Field Mount Transmitter only

NI/ I, II / 2 / ABCDFG / T4 Ta = -40°C to +60°C; Type 4X: IP65

S / III / T4 Ta = -40°C to +60°C; Type 4X: IP65

DIP / II, III / 1 / EFG / T4 Ta = -40°C to +60°C; Type 4X: IP65

j = Temperature range of sensor/Ambient temperature range; 1, 2, 3, or 4.
k = Name plate language and type; A, B, or C
o = Cable Conduits; A, B, or C.
p = Power supply; 1, 2, 3, or 4.
q = Input and output signal type; A, B, C, or D.
r = Configuration type/Diagnostics; 0, 1, 2, 3 or 4.

Equipment Ratings:

Nonincendive for Class I, Division 2, Groups A, B, C and D; Suitable for Class II, Division 2 Groups F and G; Suitable for Class III, Divisions 1 and 2; Dust ignition Protected for Class II and III, Division 1, Groups E, F and G. Temperature Class dependent on Ambient and Process Temperature (see IDM-10-A0228); Ambient Temperature -40°C to +60°C; Indoor and outdoor locations

FM Approved for:

ABB Automation Products GmbH
D-37079 Göttingen GERMANY



Member of the FM Global Group

This certifies that the equipment described has been found to comply with the following Approval Standards and other documents:

C22.2 No. 213	1987
C22.2 No. 25	1966
C22.2 No. 142	1987
C22.2 No. 1010.1	1992

Original Project ID: 3034391C

Approval Granted: *October 1, 2008*

Subsequent Revision Reports / Date Approval Amended

Report Number	Date	Report Number	Date
---------------	------	---------------	------

FM Approvals LLC

J. E. Marquedant

 J. E. Marquedant
 Group Manager, Electrical

1 October 2008

 Date