

Technical Information

RESOLAM^â 02

Slot insulation laminates, strips, channel sections (L + U).

TYPE	Aramid aromatic polyamide fibre paper (PA).
GENERAL PROPERTIES	<p>Good electrical and mechanical properties and very good thermal material properties.</p> <p>Temperature class F - H.</p>
APPLICATION	<p>Thin insulating material especially for use as slot insulation, slot liners, insulation between layers, intermediate inserts for electrical machines in the low to medium output range.</p> <p>Slot inserts of highly flexible RESOLAM 02 are very easily fitted in position. For electrical and mechanical applications in electrical machines and equipment, operating even at high temperatures.</p>
SUPPLY	<p>STANDARD THICKNESSES: 0,25 / 0,30 / 0,38 / 0,51, Nominal: 0,76</p> <p>To special order surfaces are processed for better resistance to moisture and dirt-protection, usually by coating with clear tracking-resistant varnish.</p> <p>Channels and other sections The most common configurations are L- and U-channel sections. Micafil 's own manufacturing technology does not limit the length. Any other geometry of sections is possible to meet individual customer requirements.</p> <p>Straightness and flex The standard tests for these properties are practicable only under certain conditions. Resolam channel sections are supplied in dry condition in thermosealed plastic bags containing silicagel drying agent, which should not be opened. Once it is unpacked, geometry variations are closely dependent on the momentary moisture conditions and are also unavoidable on account of the high flexibility of PA paper.</p> <p>Testing of slot insulation In order to ensure maximum security against slot insulation failures, specimens of material and finished components are tested at regular intervals.</p>



STANDARDS RESOLAM 02 is not covered by any national or international standard specifications at the present time.

MACHINABILITY RESOLAM is easily sawn, parted and drilled. It should be machined dry.

HUMIDITY All raw materials on a fibre basis absorb humidity. However the electrical characteristics of PA paper are, comparatively speaking, only slightly influenced by the presence of humidity. On the other hand the influence of humidity on variations in length, particularly in the case of long components, is to be taken into account.

STORAGE RESOLAM-channel sections are supplied in dry condition in thermosealed plastic bags containing silicagel drying agent, which should not be opened until shortly before use of their contents. Channel sections removed from their bags and stored at over 20% relative air humidity will absorb moisture and their length will increase by 0,5% to 1%, depending on ambient moisture content. Parts can be dried as follows:

varnished parts:	70 - 80°C	(6 - 15h)
unvarnished parts:	70 - 80°C	(2 - 3h)

Channel sections unpacked prematurely for special reasons (like control-lings) should be resealed in plastic bags containing active drying agent when no longer required.

Note:

For the thickness range 0,5 to 1,5 mm consisting of several layers of aramide paper bonded with heat-resistant resin please ask for RESOLAM 03

DIMENSIONS

Table 1: Standard Dimensions and Tolerances

			L-Channel		U-Channel	
			Standard dimensions	Tolerances	Standard dimensions	Tolerances
Length	L	mm	≤12'000	+3/-0	≤12'000	+3/-0
Breadth	Ba/Bi	mm	20 - 250	± 0,15	20 - 250	± 0,15
Height	H	mm	5 - 50	± 0,15	5 - 200	± 0,15
Wall thickness	s	mm	0,5 - 2,5	± 0,1	0,5 - 2,5	± 0,1
Inside radius	Ri	mm	3	± 0,2	1	± 0,2
Outside radius	Ra	mm	Ra = Ri+s	± 0,2	Ra = Ri+s	± 0,2
Angle ¹⁾	α	°	90	± 3	90	± 3

¹⁾ Indicated angles are exact only within the bending range. The material cannot be machined to other than standard thicknesses.




Table 2: Perpendicular test voltage ⊥

The test voltage at 50 Hz, 1 minute is applied in perpendicular direction. The voltage level considers the shape and the surface of the slot insulation as well as the necessary flashover distances.		
Test voltage	Thickness s in mm	
	0,51	0,76 ¹⁾
L – channel	7,2 kV	9,5 kV
U – channel	7,2 kV	9,5 kV

¹⁾ For very short edges (one-sided) H = 3 to 10 mm, the test voltage should be reduced to 80% of flashover voltage. No side electrodes are used for this test.

RESOLAM^â 02

	Properties		Standards	Units	Values
Composition	Aramid Paper *)				
	Density:		ISO 1183	g/cm ³	0,8 - 1,0
	*) Nomex 410: Product Du Pont de Nemours & Co. Inc. USA				
	Values for thickness = s		DIN 53105	mm	0,51 0,76
Electrical properties	Electric strength \perp 50 Hz, 1 min.		IEC 243	kV	9,5 13,4
	Standard angle and channel (sections)				
	Test voltage \perp 50 Hz, 1 min.		IEC 243	kV	7,2 kV 9,5 kV
Mechanical properties	Tensile strength	MR QR	ISO 1924	N/cm	>450 >290 >650 >420
	Elongation at fracture	MR QR	ISO 1924	%	>11 >11 >11 >11
Thermal Properties	Temperature class		IEC 85	°C	F - H
	Linear thermal expansion (20 - 100°C)	MR QR	DIN 52328	K ⁻¹	20 * 10 ⁻⁶ 80 * 10 ⁻⁶

\perp perpendicular to layers
 \parallel parallel to layers
 MR machine direction along support
 QR cross direction to support

These properties have been determined by the above shown methods. The data given are valid for standard test specimen only. Unless otherwise specified, all data were measured at ambient temperature on specimen as manufactured and without particular treatment.

The contents of this publication are based on our present experience. They are an indication for application of our products without any liability for us. Notice of legal requirements and existing patent rights has to be taken. Due to the many application and manufacturing possibilities, we cannot give any warranty for the technical results in individual cases.



ABB Schweiz AG
Micafil
Badenerstrasse 780
CH-8048 Zürich
Telefon: +41 (0)58 586 03 33
Fax: +41 (0)58 586 03 01