




MS-7 800mm Electric Corner Rotate

Main Applications: Engine, Axle, Transmission Assembly



Description:

- Electric turntable to transport 800mm wide pallet and part around corner

Equipment:

- MS7 transport section
- VFD electric rotate package to control rotate and stop speed
- Limited torque roller package with constant speed drive
- 18m/min maximum conveyor speed
- 100 - 700 Kg maximum pallet weight

Customer

Benefits:

- Pallet can be rotated in any direction for versatility
- Eliminates the need for a power on/off assembly on conveyor line height is consistent. Global standard available from all ABB PTA lead centers

Global Code:

S0700-320-80

Version: A



MS-7 800mm Electric Corner Rotate

Process Parameters

Name	Values	Units	Description
Rotation:	90 (default); n/a (min); 360 (max);	degrees	Angular rotation capability of the unit
Conveyor speed:	15 (default); 2 (min); 18 (max)	m/min.	Operating speed limits of this conveyor
Standard length:	1 (default)	Meters	inches

Design Parameters

Name	Values	Units	Description
None			

Reference Projects:

ABB Inc.
1250 Brown Road
Auburn Hills, Michigan 48326
T/ 248-393-4600
F/ 248-393-4603

ABB Automation Technologies AB
Powertrain
Omformargatan 18
SE-72137 Västerås
Sweden
T/ +46-21-3600-400
F/ +46-21-3600-450

ABB Engineering Ltd.
31 Industrial Building
Fu Te Dong San Road
Waigaoqiao FTZ, Pudong
Shanghai, P. R. China 200131
T/ +86-21-6105-6666
F/ +86-21-6105-6667

www.abb.com/robotics

ABB Inc.

