



We reserve all rights in this document and in the information contained therein. Reproduction, use or distribution of this document or the information it contains is strictly forbidden. © ABB Automation Technologies AB



MULTI-FUNCTION CURRENT PROTECTION



101 RXTUG 22H
107 RXHL 411

- 1), 2) BINARY INPUT, PROGRAMMABLE
- 3)-7) RELAY OUTPUTS 1-5, PROGRAMMABLE FUNCTION
- 8) LOSS OF AUXILIARY VOLTAGE
- 9) CONNECTED FOR RL=110-220 V DC
CHANGE FROM 110 TO 112 AND 121 TO 122
AT RL=48-60 V DC

PROGRAMMABLE FUNCTIONS FOR BINARY INPUTS:
BLOCKING/ENABLING I>, I>>, I>>>, IN>, IN>>, IN>>>
THERMAL RESET 0, BREAKER FAILURE EXTERNAL START;
ALTERNATIVE SETTINGS; RESET OF LED INDICATIONS.

PROGRAMMABLE FUNCTIONS FOR BINARY OUTPUTS:
START AND TRIP I>, I>>, I>>>, IN>, IN>>, IN>>>;
THERMAL ALARM 0; THERMAL TRIP 0;
BREAKER FAILURE RE-TRIP; BREAKER FAILURE BACK-UP TRIP;
ALTERNATIVE SETTINGS; IN SERVICE

BINARY INPUT OPTIONS:
CIRCUIT-BREAKER CLOSED; CIRCUIT-BREAKER READY;
BLOCKING OF AUTORECLOSING; AUTORECLOSING EXTERNAL ON.

BINARY OUTPUT OPTIONS:
AUTORECLOSING ON; AUTORECLOSING READY;
AUTORECLOSING STARTED;
AUTORECLOSING PULSE TO CIRCUIT-BREAKER;
AUTORECLOSING UNSUCCESSFUL; INTENTIONAL OVERREACH TRIP.

Customer drw no	Prep. PTUA/ TPTD H Raza/JE 2000-03-24	1MRK 001 082-FA	Cont. sh/ No of sh
	Appr. PTUA/ Roger Karlsson 2000-03-24	Circuit Diagram	
	Resp. dept PTUA/ TPTD	Multi-f current prot.	
Based on	ABB Automation Technologies		Document number
		1MRK001083-FA	Lang. en
			Rev. A
			Sheet 1

Document status: Approved